

Garant
Machine tap, TiCN, M: M3

Order data

Order number	135370 M3
GTIN	4045197076670
Item class	11H

Description
Version:

With strong right-hand chip flutes, for optimum swarf evacuation.

For use with **emulsion** (fat content minimum 8%).

Improved wear characteristics due to optimised HSS-E tool material

Recommendation:

For **TOOLOX materials we recommend deviating from the DIN data** (see table) by drilling the tapping hole \varnothing **0.05** to **0.3 mm** larger.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 56 mm

Shank \varnothing D_s: 3.5 mm

Shank square □: 2.7 mm

Tapping hole \varnothing : 2.5 mm

Technical description

Number of clamping slots	3
Number of cutting edges Z	3
Thread pitch	0.5 mm
Tapping hole \varnothing	2.5 mm
Thread \varnothing	3 mm
Standard	DIN 371

Shank $\varnothing D_s$	3.5 mm
Overall length L	56 mm
Shank square \square	2.7 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	6 mm
Thread type	M
Thread size	M3
Coating	TiCN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	19 m/min	P
Steel < 900 N/mm ²	suitable	19 m/min	P
Steel < 1100 N/mm ²	suitable	9 m/min	P
Steel < 1400 N/mm ²	suitable	4 m/min	P
TOOLOX 33	suitable	3 m/min	H

Oil	suitable
wet maximum	suitable