

**Garant**
**Machine tap HSS-E-PM, TiN / vaporised, M: M5**

**Order data**

Order number	135375 M5
GTIN	4045197197924
Item class	11H

**Description**
**Version:**

For use with **emulsion** (fat content minimum 8%).

For use with **emulsion** (fat content minimum 8%).

**Recommendation:**

For **TOOLOX** and **HARDOX materials** we recommend **deviating from the DIN data** (see table) by drilling the tapping hole  $\varnothing$  **0.05** to **0.3 mm** larger.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.8 mm

Overall length L: 70 mm

Shank  $\varnothing$  D<sub>s</sub>: 6 mm

Shank square □: 4.9 mm

Tapping hole  $\varnothing$ : 4.2 mm

**Technical description**

Tapping hole $\varnothing$	4.2 mm
Number of clamping slots	3
Thread $\varnothing$	5 mm
Thread pitch	0.8 mm
Number of cutting edges Z	3
Standard	DIN 371
Shank $\varnothing$ D <sub>s</sub>	6 mm

Overall length L	70 mm
Shank square □	4.9 mm
Tolerance class	ISO 2 6H
Tool material	HSS E PM
Thread depth	15 mm
Thread type	M
Thread size	M5
Coating	TiN / vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	red
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	27 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	23 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	23 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	13 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	10 m/min	P
TOOLOX 33	suitable	12 m/min	H
Ti > 850 N/mm <sup>2</sup>	suitable	5 m/min	S

Oil	suitable
wet maximum	suitable