

Garant
Machine tap tapered, vaporised, M: M3

Order data

Order number	135550 M3
GTIN	4045197076946
Item class	11H

Description
Version:
With conically offset guide thread.
Particularly for recessed blind hole threads where the swarf generated remains in the tap flutes. **HSS-E**

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 56 mm

Shank $\varnothing D_s$: 3.5 mm
Shank square \square : 2.7 mm
Tapping hole \varnothing : 2.5 mm

Technical description

Tapping hole \varnothing	2.5 mm
Thread \varnothing	3 mm
Thread pitch	0.5 mm
Number of clamping slots	3
Number of cutting edges Z	3
Standard	DIN 371
Shank $\varnothing D_s$	3.5 mm
Overall length L	56 mm

Shank square <input type="checkbox"/>	2.7 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	6 mm
Thread type	M
Thread size	M3
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	15 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M

CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		
wet maximum	suitable only under restricted conditions		