



HOLEX Pro Tap machine tap HSS-E, TiN, UNF: 7/8-14



Order data

Order number	138050 7/8-14
GTIN	4062406374983
Item class	12I

Description

Version:

HOLEX Pro Tap general-purpose tap. Sturdy design suitable for a wide spectrum of materials.
Improved HSS-E tool material with low-friction TiN coating.

Application:

For UNF uniform fine threads ASME – B1.1.

Technical description

Number of cutting edges Z	4
Overall length L	125 mm
Thread pitch	1.814 mm
Tapping hole \varnothing	20.4 mm
Shank square \square	14.5 mm
Thread size	7/8-14 UNF
Thread \varnothing	22.23 mm
Thread depth	55.56 mm
Thread type	UNF
Number of clamping slots	4
Tool material	HSS E
Standard	DIN 374

Threads per inch	14
Shank $\varnothing D_s$	18 mm
Series	Pro Tap
Coating	TiN
Flank angle	60°
Tolerance class	2B
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	25 m/min	N
Alu > 10% Si	suitable	10 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P
Steel < 750 N/mm ²	suitable	20 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	8 m/min	P
INOX < 900 N/mm ²	suitable	8 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N

Uni	suitable
Oil	suitable
wet maximum	suitable