



Carbide saw blade, Type: 165T24



Order data

Order number	078212 165T24
GTIN	4002395369720
Item class	07A

Description

Version:

PTFE coating (Teflon): reduces friction for quicker and cooler cutting. Protects against corrosion and accumulation of resin. Laser-cut vibration slots: for lower vibration and more precise cutting. Slots are filled with polyurethane and operate as shock absorbers because the vibrations do not penetrate into the carbide teeth. High-quality laser-cut steel: guaranteed precise cutting. Carbide teeth offset with cobalt: remain sharp longer and for clean cutting. Optimised for cordless tools, extra-thin cutting width for long a working life per battery charge. All types of wood: Softwood/hardwood, plywood, coated panels, melamine, MDF. Standard saw blades without Teflon coating and vibration slots.

Technical description

Blade Ø D	165 mm
Bore Ø	15.87 mm
Number of teeth	24
Suitable for materials	wood

Type of product

Circular saw blade