

**Cordless hammer drill, Type: GBH18V45C****Order data**

Order number	P07551 GBH18V45C
GTIN	3165140915427
Item class	03B

Description**Version:**

- **Lighter than comparable products with cables thanks to the highly optimised drive train – also with ProCORE18V 12.0Ah.**
- **Comfort while working thanks to Lock-on Button for continuous chisel work.**
- **Maximum power thanks to BITURBO technology.**
- **Precise work results thanks to speed setting for variable speeds.**
- **Improved visibility due to LED work light.**
- **Kick Back Control to reduce risks from sudden tool reactions.**
- **Equipped with Soft-Start, ASC and EPC for top user protection.**
- **Flexible work thanks to individual configuration depending on the application, using the Bosch My Tools app.**

Supplied with:

Including additional handle, connectivity module, machine cloth and case.

Technical description

maximum hammer rate	2720 min ⁻¹
Packaging	Carrying case
maximum twist drill size Ø in concrete	45 mm
Speed range	0 min ⁻¹
Manufacturer's designation	GBH 18V-45 C

Number of rechargeable batteries contained	0
Impact energy	12.5 J
Power supply	Rechargeable battery-powered
suitable battery - supplier / battery type / voltage	Bosch 18 V
Battery voltage	18 V
Weight including rechargeable battery	8.9 kg
Type of rechargeable battery	Lithium-ion
maximum vibration to EN	8.5 m/s ²
Length	442 mm
Height	224 mm
Weight without battery	8 kg
Type of product	Hammer drill