



HOLEX Pro Tap machine tap HSS-E Form C, TiN, M: M5



Order data

Order number	135910 M5
GTIN	4062406374426
Item class	12I

Description

Version:

Form C (2–3 turns lead chamfer).

HOLEX Pro Tap general-purpose tap. Sturdy design suitable for a wide spectrum of materials.

Improved HSS-E tool material with **friction-reduction TiN coating**.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.8 mm

Overall length L: 70 mm

Shank $\varnothing D_s$: 6 mm

Shank square \square : 4.9 mm

Tapping hole \varnothing : 4.2 mm

Technical description

Thread pitch	0.8 mm
Thread type	M
Number of clamping slots	3
Standard	DIN 371
Thread \varnothing	5 mm
Thread size	M5
Tolerance class	ISO 2 6H
Number of cutting edges Z	3

Tapping hole \varnothing	4.2 mm
Shank $\varnothing D_s$	6 mm
Tool material	HSS E
Thread depth	15 mm
Overall length L	70 mm
Shank square \square	4.9 mm
Coating	TiN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	25 m/min	N
Alu > 10% Si	suitable	10 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P
Steel < 750 N/mm ²	suitable	20 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P

Steel < 1100 N/mm ²	suitable only under restricted conditions	8 m/min	P
INOX < 900 N/mm ²	suitable	8 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		