

## Garant

### GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM, TiAlN, G: G1/8



#### Order data

Order number	139415 G1/8
GTIN	4062406375133
Item class	11I

#### Description

##### Version:

**DIN 2189** (≈ DIN 5156). **With oil grooves; optimum lubrication effect even in deeper threads.**

##### GARANT Master Form Steel:

The latest generation of high-performance fluteless taps, specially developed for **use in steels.**

- **Optimised polygon geometry for a lower torque.**
- **Multi-layer HIPIMS coating for high wear resistance.**
- **HSS-E-PM substrate for top process reliability.**

##### Application:

For **Whitworth parallel pipe threads** DIN-ISO 228/1 (threads that do not form a seal within the connection).

Thread pitch: 0.907 mm

Threads per inch: 28

Thread Ø: 9.73 mm

Overall length L: 90 mm

Shank Ø D<sub>s</sub>: 7 mm

Shank square □: 5.5 mm

#### Technical description

Number of cutting edges Z	6
Number of clamping slots	6
Threads per inch	28
Shank square □	5.5 mm

Thread depth	29.19 mm
Thread Ø	9.73 mm
Overall length L	90 mm
Thread pitch	0.907 mm
Shank Ø D <sub>s</sub>	7 mm
Tapping hole Ø guide value	9.25 mm
Thread size	G1/8
Coating	TiAlN
Thread type	G
Flank angle	55 °
Tool material	HSS E PM
Standard	DIN 2189
Tolerance class	ISO 228 X
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Colour ring	blue
Type of product	Fluteless tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	38 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	37 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	35 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	27 m/min	P

Steel < 1100 N/mm <sup>2</sup>	suitable	18 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	12 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	12 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable only under restricted conditions	7 m/min	M
CuZn	suitable only under restricted conditions	22 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		