



HOLEX Pro Tap machine tap HSS-E, TiN, G: G3/8



Order data

Order number	133332 G3/8
GTIN	4062406374143
Item class	12I

Description

Version:

HOLEX Pro Tap general-purpose tap. Sturdy design suitable for a wide spectrum of materials. **Improved HSS-E tool material with low-friction TiN coating.**

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS E

Threads per inch: 19

Thread Ø: 16.66 mm

Overall length L: 100 mm

Shank Ø D_s: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 15.25 mm

Technical description

Threads per inch	19
Number of clamping slots	2
Number of cutting edges Z	2
Overall length L	100 mm
Thread size	G3/8
Tapping hole Ø	15.25 mm
Shank square □	9 mm

Shank $\varnothing D_s$	12 mm
Thread \varnothing	16.66 mm
Thread pitch	1.337 mm
Tool material	HSS E
Thread depth	49.98 mm
Coating	TiN
Thread type	G
Flank angle	55 °
Standard	DIN 5156
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	24 m/min	N
Aluminium (short chipping)	suitable	25 m/min	N
Alu > 10% Si	suitable	10 m/min	N
Steel < 500 N/mm ²	suitable	24 m/min	P
Steel < 750 N/mm ²	suitable	20 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	8 m/min	P

INOX < 900 N/mm ²	suitable	8 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		