

Garant
GARANT Diabolo solid carbide deburrer, spiral flutes 60°, TiAlN, Ø h6 DC: 6Mmm

Order data

Order number	208167 6M
GTIN	4062406380410
Item class	11X

Description
Version:

Outstanding surface qualities thanks to the **35° helix angle**.

Deburrer specially developed for **hard machining**. The further development of the DIABOLO coating permits even longer tool life and improved surface quality.

Tolerance: **Dimension S = ± 0.2 mm. Point angle ±5 arc minutes**. Extra-long deburrers for outstanding deburring results on particularly difficult-to-access contours. Tools without tip.

Application:

Perfectly suitable for **chamfering** and **deburring** component edges and for **contouring applications**.

Technical description

Shank Ø D _s	6 mm
No. of teeth Z	6
Chamfer mill	30 degrees
Shank	DIN 6535 HA to h6
Feed f _z in steel < 60 HRC	0.02 mm
small Ø D ₃	3 mm
Dimension S	2.9 mm
Series	Diabolo
Cutting edge Ø D _c	6 mm

large Ø D ₂	6 mm
Corner chamfer angle	60 degrees
Overall length L	100 mm
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal Ø	h6
Helix angle	35 degrees
Direction of infeed	horizontal and oblique
Countersink tip angle	60 degrees
Through-coolant	no
Shank tolerance	h6
Colour ring	red
Type of product	Deburrers

User data

	Suitability	V _c	ISO code
Steel < 1100 N/mm ²	Suitable only under restricted conditions	140 m/min	P
Steel < 1400 N/mm ²	suitable	120 m/min	P
Steel < 55 HRC	suitable	100 m/min	H
Steel < 60 HRC	suitable	90 m/min	H
Steel < 65 HRC	suitable	60 m/min	H
Steel < 67 HRC	Suitable only under restricted conditions	35 m/min	H
wet minimum	Suitable only under restricted conditions		
dry	suitable		
Air	suitable		

