

SONO+SWISS®

Ultrasonic power cleaner T5, Capacity l/kg: 2,5



Order data

Order number

082935 2,5

GTIN

Item class

04E

Description

Version:

High-yield water-based cleaning concentrate (exception: T3 supplied in powdered form); specially developed for use in ultrasonic cleaning baths; biologically degradable. The high-yielding **concentrates** extend the working life of the devices, last a long time, and are biologically degradable. The power cleaners have been specially developed for ultrasonic baths (foaming characteristics etc.) and are therefore particularly effective for all conventional ultrasonic cleaning baths operating at frequencies in the range 25 to 130 kHz. In conjunction with the cavitation forces created by the ultrasonic vibration the power cleaner releases the dirt gently but effectively whilst treating the components gently. Other cleaning agents which have not been developed specially for ultrasonic baths may under certain circumstances promote corrosion or removal of material. Halogen ions are an example of aggressive corrosion promoters which greatly reduce the working life. Chlorides and fluorides in acid media are the most aggressive in this respect.

Application:

For ultrasonic cleaning baths (such as No. 082922; 082923; 082924; 082925).

Note:

Other special cleaners and other container sizes available on request. 25-litre drums are available in the online shop.

Unavailable in some countries.

Technical description

Fill capacity liquid	2.5 l
Type of cleaning agent	Weak acid cleaner
Labelling of hazardous substances	GHS07: Exclamation mark
Storage temperature	-5 - 30 °C
Mixing ratio	1 – 5 %
Manufacturer's designation	T5
Processing time	2 min
Type of product	Ultrasonic power cleaner