

SONO+SWISS®

Ultrasonic power cleaner T5, Capacity l/kg: 10**Order data**

Order number	082935 10
GTIN	2050002050372
Item class	04E

Description**Version:**

High-yield water-based cleaning concentrate (exception: T3 supplied in powdered form); specially developed for use in ultrasonic cleaning baths; biologically degradable. The high-yielding **concentrates** extend the working life of the devices, last a long time, and are biologically degradable. The power cleaners have been specially developed for ultrasonic baths (foaming characteristics etc.) and are therefore particularly effective for all conventional ultrasonic cleaning baths operating at frequencies in the range 25 to 130 kHz. In conjunction with the cavitation forces created by the ultrasonic vibration the power cleaner releases the dirt gently but effectively whilst treating the components gently. Other cleaning agents which have not been developed specially for ultrasonic baths may under certain circumstances promote corrosion or removal of material. Halogen ions are an example of aggressive corrosion promoters which greatly reduce the working life. Chlorides and fluorides in acid media are the most aggressive in this respect.

Application:

For ultrasonic cleaning baths (such as No. 082922; 082923; 082924; 082925).

Note:

Other special cleaners and other container sizes available on request. 25-litre drums are available in the online shop.

Unavailable in some countries.

Technical description

Storage temperature	-5 - 30 °C
Type of cleaning agent	Weak acid cleaner
Manufacturer's designation	T5
Mixing ratio	1 – 5 %
Fill capacity liquid	10 l
Processing time	2 min
Labelling of hazardous substances	GHS07: Health hazard
Type of product	Ultrasonic power cleaner