


## Garant

### GARANT Master Alu PickPocket solid carbide roughing end mill HPC, DLC, Ø e6 DC: 20mm



#### Order data

Order number	202010 20
GTIN	4062406380854
Item class	11X

#### Description

##### Version:

For roughing and finishing.

Up to  $2 \times D$  into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to  $45^\circ$ .

With the latest generation of DLC coating  $sp^2$ .

##### Advantage:

**Optimised flute form, eccentric relief ground, generous chip spaces.**

#### Technical description

Feed $f_z$ for slot milling in short-chipping aluminium	0.16 mm
Corner rounding $r_v$	0.2 mm
Shank	DIN 6535 HA to h6
Flute length $L_c$	60 mm
Feed $f_z$ for side milling in short-chipping aluminium	0.18 mm
Recess $\varnothing D_1$	19.8 mm
Helix angle	42 degrees
Shank $\varnothing D_s$	20 mm
Cutting edge $\varnothing D_c$	20 mm
Direction of infeed	horizontal, oblique and vertical

Overall length L	126 mm
Tolerance nominal $\varnothing$	e6
Balance quality with shank	G 2.5 with HA
No. of teeth Z	3
Overhang length $L_1$ incl. recess	74 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Cutting width $a_e$ for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	Suitable	550 m/min	N
Aluminium (short chipping)	suitable	500 m/min	N
Alu > 10% Si	suitable	450 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N

PF 31	Suitable	130 m/min	N
PVDF GF20	Suitable	180 m/min	N
POM GF25	Suitable	160 m/min	N
PA 66 GF30	Suitable	150 m/min	N
PEEK GF30	Suitable	130 m/min	N
PTFE CF25	Suitable	160 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
<b>Air Services</b>	Suitable		

Shank grinding Type HB

129100 HB