

GARANT Master Form Steel fluteless machine tap with oil grooves HSS-E-PM IC, TiAIN, MF: 5X0,5



Order data

Order number	139290 5X0,5
GTIN	4062406375126
Item class	111

Description

Version:

GARANT Master Form Steel:

The latest generation of **high-performance fluteless taps** are specially developed for **use in steels.**

- · Optimised polygon geometry for a reduced torque.
- · Multi-layer HIPIMS coating for high wear resistance.
- · HSS-E-PM substrate for top process reliability.

DIN 2174 (\approx DIN 371 \leq M10; DIN 376 \geq M12).

With internal coolant feed laterally from the grooves. Permits the longest possible tool life when machining through holes and blind holes.

Tolerance class: ISO 2X 6HX Thread pitch: 0.5 mm Overall length L: 70 mm

Shank Ø D₅: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø guide value: 4.8 mm

Technical description

Thread size	M5×0.5	
Tapping hole Ø guide value	4.8 mm	
Series	GARANT Master	
Thread pitch	0.5 mm	

Shank Ø D _s	6 mm		
Thread Ø	5 mm		
Number of clamping slots	5		
Overall length L	70 mm		
Shank square □	4.9 mm		
Number of cutting edges Z	5		
Thread depth	15 mm		
Tolerance class	ISO 2X 6HX		
Coating	TiAIN		
Thread type	MF		
Flank angle	60 °		
Tool material	HSS E PM		
Standard	DIN 2174		
Thread standard	DIN 13		
Taper lead form	С		
Shank	Plain shank with h9		
Through-coolant	yes		
Application for type of drilling	up to 3×D for blind holes		
Application for type of drilling	up to 3×D for through holes		
Cutting direction	right-hand		
Colour ring	without		
Type of product	Fluteless tap		

User data

	Suitability	\mathbf{V}_{c}	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	42 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	Р
Steel < 750 N/mm ²	suitable	38 m/min	Р

Steel < 900 N/mm ²	suitable	29 m/min	Р
Steel < 1100 N/mm ²	suitable	20 m/min	Р
Steel < 1400 N/mm ²	suitable	15 m/min	Р
INOX < 900 N/mm ²	suitable	15 m/min	М
INOX > 900 N/mm ²	suitable only under restricted conditions	8 m/min	М
CuZn	suitable only under restricted conditions	25 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		