

**Garant**
**GARANT Master Alu PickPocket solid carbide roughing end mill HPC, DLC, Ø e6 DC: 10mm**

**Order data**

Order number	202017 10
GTIN	4062406381042
Item class	11X

**Description**
**Version:**

For roughing and finishing.

Up to  $2 \times D$  into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to  $45^\circ$ .

Very long overhang for safe machining of deep cavities.

With the latest generation of DLC coating  $sp^2$ .

**Advantage:**

**Optimised flute form, eccentric relief ground, generous chip spaces.**

**Note:**

A minimum oversize of  $0.1 \times D$  must be maintained for subsequent finishing operations.

**Technical description**

Overall length L	100 mm
Overhang length $L_1$ incl. recess	58 mm
Helix angle	42 degrees
No. of teeth Z	3
Shank $\varnothing D_s$	10 mm
Feed $f_z$ for slot milling in short-chipping aluminium	0.05 mm
Shank	DIN 6535 HA to h6
Feed $f_z$ for side milling in short-chipping aluminium	0.07 mm

Recess $\varnothing D_1$	9.2 mm
Balance quality with shank	G 2.5 with HA
Cutting edge $\varnothing D_c$	10 mm
Tolerance nominal $\varnothing$	e8
Flute length $L_c$	16 mm
Direction of infeed	horizontal, oblique and vertical
Corner rounding $r_v$	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Aluminium	Suitable	380 m/min	N
Aluminium (short chipping)	suitable	300 m/min	N
Alu > 10% Si	Suitable	270 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N

PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N
PVDF GF20	Suitable	160 m/min	N
POM GF25	Suitable	150 m/min	N
PA 66 GF30	Suitable	140 m/min	N
PEEK GF30	Suitable	120 m/min	N
PTFE CF25	Suitable	150 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	220 m/min	N
Cu	Suitable	140 m/min	N
CuZn	Suitable	160 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		