

Garant

GARANT Master Alu PickPocket solid carbide roughing end mill HPC, DLC, Ø e6 DC: 16mm



Order data

Order number	202017 16
GTIN	4062406381066
Item class	11X

Description

Version:

For roughing and finishing.

Up to $2 \times D$ into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to 45° .

Very long overhang for safe machining of deep cavities.

With the latest generation of DLC coating sp^2 .

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Note:

A minimum oversize of $0.1 \times D$ must be maintained for subsequent finishing operations.

Technical description

Balance quality with shank	G 2.5 with HA
Direction of infeed	horizontal, oblique and vertical
Overall length L	150 mm
Overhang length L_1 incl. recess	100 mm
No. of teeth Z	3
Feed f_z for side milling in short-chipping aluminium	0.1 mm
Helix angle	42 degrees
Cutting edge $\varnothing D_c$	16 mm

Shank	DIN 6535 HA to h6
Feed f_z for slot milling in short-chipping aluminium	0.08 mm
Recess $\varnothing D_1$	15 mm
Corner rounding r_v	0.2 mm
Shank $\varnothing D_s$	16 mm
Tolerance nominal \varnothing	e8
Flute length L_c	25 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	380 m/min	N
Aluminium (short chipping)	suitable	300 m/min	N
Alu > 10% Si	Suitable	270 m/min	N
PMMA acrylic	Suitable	180 m/min	N
PE-HD	Suitable	130 m/min	N
PA 66	Suitable	150 m/min	N

PEEK	Suitable	130 m/min	N
PF 31	Suitable	110 m/min	N
PVDF GF20	Suitable	160 m/min	N
POM GF25	Suitable	150 m/min	N
PA 66 GF30	Suitable	140 m/min	N
PEEK GF30	Suitable	120 m/min	N
PTFE CF25	Suitable	150 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	220 m/min	N
Cu	Suitable	140 m/min	N
CuZn	Suitable	160 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		