

Garant

Solid carbide NC machine reamer Configurable, uncoated, Nominal \varnothing DC: 2,2mm



Order data

Order number	164345 2,2
GTIN	4045197328175
Item class	10N

Description

Version:

Version suitable for NC DIN 8093-2 with straight shank \varnothing for standard chucking especially in **hydraulic chucks** or **high precision collet chucks**. This ensures **very high concentricity** and **process reliability**,

The use of GARANT-NC reamers eliminates the need to procure special collets. With long flutes and left-hand helix.

Reamers finish ground to match your specification.

Application:

For reaming through holes, as the chips are evacuated in the cutting direction. Lead taper is suitable also for blind holes.

Note:

For H7 fit see No. 164340 and 164341.

Technical description

Shank tolerance	h6
Feed f in steel < 1100 N/mm ²	0.1 mm/rev.
Overhang L ₁	19 mm
Nominal \varnothing D _c	2.2 mm
Shank \varnothing D _s	4 mm
Overall length L	50 mm
Flute length L _c	12 mm
\varnothing range	2.13 - 2.36 mm

Number of cutting edges Z	4
Reaming oversize in diameter	0.05 - 0.1 mm
Coating	uncoated
Tool material	Solid carbide
Standard	DIN 8093
Through-coolant	no
Shank	DIN 6535 HA with h6
Application for type of drilling	for through holes
Colour ring	green
Type of product	Phillips bit

User data

	Suitability	V _c	ISO code
Aluminium	suitable	35 m/min	N
Aluminium (short chipping)	suitable	30 m/min	N
Steel < 500 N/mm ²	suitable	20 m/min	P
Steel < 750 N/mm ²	suitable	13 m/min	P
Steel < 900 N/mm ²	suitable	10 m/min	P
Steel < 1100 N/mm ²	suitable	8 m/min	P
Steel < 1400 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	10 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	8 m/min	M
Ti > 850 N/mm ²	suitable	8 m/min	S
GG(G)	suitable	8 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
wet maximum	suitable		

