

**HOLEX®**
**Die HSS-E, M× pitch: 8X0,75**

**Order data**

Order number	141065 8X0,75
GTIN	4045197595287
Item class	12K

**Description**
**Version:**

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

**2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.**

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 0.75 mm

External Ø: 25 mm

Height: 9 mm

**Technical description**

Height	9 mm
Pitch	0.75 mm
External Ø	25 mm

Tolerance class	DIN 13 6g
Thread size	8
Thread type	MF
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand