

Garant
Solid carbide NC machine reamer Configurable, uncoated, Nominal Ø DC: 2,5mm

Order data

| | |
|--------------|---------------|
| Order number | 164345 2,5 |
| GTIN | 4045197328182 |
| Item class | 10N |

Description
Version:

Version suitable for NC DIN 8093-2 with straight shank Ø for **standard chucking** especially in **hydraulic chucks** or **high precision collet chucks**. This ensures **very high concentricity** and **process reliability**,

The use of GARANT-NC reamers eliminates the need to procure special collets. With long flutes and left-hand helix.

Reamers finish ground to match your specification.

Application:

For reaming through holes, as the chips are evacuated in the cutting direction. Lead taper is suitable also for blind holes.

Note:

For H7 fit see No. 164340 and 164341.

Technical description

| | |
|--|----------------|
| Feed f in steel < 1100 N/mm ² | 0.1 mm/rev. |
| Nominal Ø D _c | 2.5 mm |
| Overhang L ₁ | 29 mm |
| Shank tolerance | h6 |
| Shank Ø D _s | 4 mm |
| Overall length L | 60 mm |
| Flute length L _c | 16 mm |
| Ø range | 2.37 - 2.65 mm |

| | |
|----------------------------------|---------------------|
| Number of cutting edges Z | 4 |
| Reaming oversize in diameter | 0.05 - 0.1 mm |
| Coating | uncoated |
| Tool material | Solid carbide |
| Standard | DIN 8093 |
| Through-coolant | no |
| Shank | DIN 6535 HA with h6 |
| Application for type of drilling | for through holes |
| Colour ring | green |
| Type of product | Phillips bit |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Aluminium | suitable | 35 m/min | N |
| Aluminium (short chipping) | suitable | 30 m/min | N |
| Steel < 500 N/mm ² | suitable | 20 m/min | P |
| Steel < 750 N/mm ² | suitable | 13 m/min | P |
| Steel < 900 N/mm ² | suitable | 10 m/min | P |
| Steel < 1100 N/mm ² | suitable | 8 m/min | P |
| Steel < 1400 N/mm ² | suitable | 6 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 10 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 8 m/min | M |
| Ti > 850 N/mm ² | suitable | 8 m/min | S |
| GG(G) | suitable | 8 m/min | K |
| CuZn | suitable | 20 m/min | N |
| Uni | suitable | | |
| wet maximum | suitable | | |

