

HOLEX®
Die HSS-E, M× pitch: 10X1

Order data

| | |
|--------------|---------------|
| Order number | 141065 10X1 |
| GTIN | 4045197595300 |
| Item class | 12K |

Description
Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1 mm

External Ø: 30 mm

Height: 11 mm

Technical description

| | |
|------------|-------|
| Pitch | 1 mm |
| Height | 11 mm |
| External Ø | 30 mm |

| | |
|-------------------|------------|
| Tolerance class | DIN 13 6g |
| Thread size | 10 |
| Thread type | MF |
| Flank angle | 60 degrees |
| Tool material | HSS E |
| Norm | EN 22568 |
| Cutting direction | right-hand |