

HOLEX®
Die HSS-E, M× pitch: 12X1

Order data

Order number	141065 12X1
GTIN	4045197595324
Item class	12K

Description
Version:

Closed, pre-slit form, **with tapered lead chamfer on both sides.**

2 turns lead chamfer. Lapped and nitrided, rake approx. 15°. For stainless and high-tensile steels.

Thread type: MF

Flank angle: 60 degrees

Tool material: HSS E

Norm: EN 22568

Tolerance class: DIN 13 6g

Pitch: 1 mm

External Ø: 38 mm

Height: 10 mm

Technical description

Pitch	1 mm
Height	10 mm
External Ø	38 mm

Tolerance class	DIN 13 6g
Thread size	12
Thread type	MF
Flank angle	60 degrees
Tool material	HSS E
Norm	EN 22568
Cutting direction	right-hand