

Garant**Hand tap, single Plug tap, uncoated, M: M16****Order data**

Order number	130180 M16
GTIN	4045197066046
Item class	11G

Description**Version:**

Size M2.3 and M2.6 to old DIN profile.

Thread type: M

Tool material: HSS

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 70 mm

Shank $\varnothing D_s$: 12 mmShank square \square : 9 mmTapping hole \varnothing : 14 mm**Technical description**

Thread pitch	2 mm
Thread \varnothing	16 mm
Tapping hole \varnothing	14 mm
Standard	DIN 352
Shank $\varnothing D_s$	12 mm
Overall length L	70 mm
Shank square \square	9 mm
Tolerance class	ISO 2 6H
Tool material	HSS

Thread depth	32 mm
Thread type	M
Thread size	M16
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
GG(G)	suitable only under restricted conditions		

Uni	suitable only under restricted conditions
Oil	suitable
dry	suitable only under restricted conditions