

Garant
Machine tap for synchronised spindles HSS-E-PM IC / Form C, TiAlN, M: M10

Order data

Order number	135746 M10
GTIN	4045197508331
Item class	11H

Description
Version:

Sturdy version with right-hand helix and shank to DIN 1835-B. Special geometry for use on machines with **synchronised spindle drives**. The tap is controlled by the synchronising spindle of the machine.

Special **TiAlN coating** for optimum tool life. For use with **emulsion** (fat content minimum 8%). With **internal coolant supply** for maximum tool life.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures very high process reliability.

Thread type: M

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank $\varnothing D_s$: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 8.5 mm

Technical description

Tapping hole \varnothing	8.5 mm
Thread \varnothing	10 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread pitch	1.5 mm

Standard	Manufacturer's standard
Shank $\varnothing D_s$	10 mm
Overall length L	100 mm
Shank square \square	8 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	25 mm
Thread type	M
Thread size	M10
Coating	TiAlN
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	DIN 1835 B to h6
Through-coolant	yes
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	blue
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	32 m/min	N
Steel < 750 N/mm ²	suitable	32 m/min	P
Steel < 900 N/mm ²	suitable	20 m/min	P

INOX < 900 N/mm ²	suitable	11 m/min	M
INOX > 900 N/mm ²	suitable	9 m/min	M
CuZn	suitable only under restricted conditions	30 m/min	N
Oil	suitable		
wet maximum	suitable		
wet minimum	suitable		