

Garant
Machine tap HSS-E-PM, nitrided, M: M2,5

Order data

Order number	135750 M2,5
GTIN	4045197077394
Item class	11H

Description
Version:
Sturdy design, with 15° right-hand chip flutes.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 0.45 mm

Overall length L: 50 mm

 Shank $\varnothing D_s$: 2.8 mm

 Shank square \square : 2.1 mm

 Tapping hole \varnothing : 2.05 mm

Technical description

Tapping hole \varnothing	2.05 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread pitch	0.45 mm
Thread \varnothing	2.5 mm
Standard	DIN 371
Shank $\varnothing D_s$	2.8 mm
Overall length L	50 mm
Shank square \square	2.1 mm

Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	5 mm
Thread type	M
Thread size	M2.5
Coating	nitrided
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	15°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	pink
Type of product	Tap

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable only under restricted conditions	18 m/min	P
Steel < 1100 N/mm ²	suitable	9 m/min	P
Steel < 1400 N/mm ²	suitable	3 m/min	P
Ti > 850 N/mm ²	suitable	4 m/min	S
Oil	suitable		
wet maximum	suitable		