

**Garant**
**Solid carbide reamer HPC blind hole, DLC, Nominal  $\varnothing$  DC: 6,5 mm**

**Order data**

Order number	164347 6,5
GTIN	4045197548801
Item class	10N

**Description**
**Version:**

**Version suitable for NC** with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With the latest generation of **DLC coating  $sp^2$** .

**Application:**

For **HPC/HSC reaming of blind holes**.

Number of cutting edges Z: 6

$\varnothing$  range: 6.21 - 6.7 mm

Flute length  $L_c$ : 16 mm

Overhang  $L_1$ : 59 mm

Overall length L: 100 mm

Number of cutting edges Z: 6

Shank  $\varnothing D_s$ : 8 mm

**Technical description**

Nominal $\varnothing D_c$	6.5 mm
Feed f in cast alu	1.2 mm/rev.
Overhang $L_1$	59 mm
Shank tolerance	h6
Shank $\varnothing D_s$	8 mm
Overall length L	100 mm

Flute length $L_c$	16 mm
Ø range	6.21 - 6.7 mm
Number of cutting edges Z	6
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	yellow
Type of product	Reaming tool with non-detachable cutters