

Garant
Solid carbide reamer HPC blind hole, DLC, Nominal \varnothing DC: 4 mm

Order data

Order number	164347 4
GTIN	4045197548757
Item class	10N

Description
Version:

Version suitable for NC with straight shank \varnothing for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

Reamers finish ground to match your specifications.

With the latest generation of **DLC coating sp^2** .

Application:

For **HPC/HSC reaming of blind holes**.

Number of cutting edges Z: 4

\varnothing range: 3.7 - 4.2 mm

Flute length L_c : 12 mm

Overhang L_1 : 34 mm

Overall length L: 75 mm

Number of cutting edges Z: 4

Shank $\varnothing D_s$: 6 mm

Technical description

Shank tolerance	h6
Overhang L_1	34 mm
Nominal $\varnothing D_c$	4 mm
Feed f in cast alu	0.6 mm/rev.
Shank $\varnothing D_s$	6 mm
Overall length L	75 mm

Flute length L_c	12 mm
Ø range	3.7 - 4.2 mm
Number of cutting edges Z	4
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	yellow
Type of product	Reaming tool with non-detachable cutters