

**Garant****Hand tap set, uncoated, MF: 8X0,5****Order data**

Order number	130470 8X0,5
GTIN	4045197066930
Item class	11G

**Description****Version:**

2-piece set **comprising taper and plug tap**. Thread ground with radial thread relief.

Thread type: MF

Tool material: HSS

Standard: DIN 2181

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 50 mm

Shank Ø D<sub>s</sub>: 6 mm

Shank square □: 4.9 mm

Tapping hole Ø: 7.5 mm

**Technical description**

Thread Ø	8 mm
Thread pitch	0.5 mm
Tapping hole Ø	7.5 mm
Shank Ø D <sub>s</sub>	6 mm
Overall length L	50 mm
Shank square □	4.9 mm
Tolerance class	ISO 2 6H

Tool material	HSS
Standard	DIN 2181
Thread depth	16 mm
Thread type	MF
Thread size	M8×0.5
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	C
Taper lead form	D
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm <sup>2</sup>	suitable		
Steel < 750 N/mm <sup>2</sup>	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		

GG(G)	suitable only under restricted conditions
Uni	Suitable
Oil	suitable
dry	suitable only under restricted conditions