

Garant
VC.T 160404, Grade: HU7315-1


Order data

Order number	261372 HU7315-1
GTIN	4062406381462
Item class	21G

Description

VC.T 160404 HU7315-1 Grade: HU7315-1
 Chip breaker: AF
 Tolerance: G
 Cutting depth a_p : 0.05 - 1.5 mm
 Feed f : 0.03 - 0.25 mm/rev.
 Cutting speed v_c main application: 50 - 600 m/min

Technical description

ISO code indexable insert	VCGT 160404
Cutting conditions	continuous
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	50 - 600 m/min
Grade	HU7315-1
Coating	uncoated

Corner radius	0.4 mm
Feed f	0.03 - 0.25 mm/rev.
Tool material	Carbide
Tolerance	G
Number of changes/inserts	2
Chip breaker	AF
Main application	N
Cutting depth a_p	0.05 - 1.5 mm
Type of product	Indexable insert for turning