



Hand tap set, uncoated, G: G1/8



Order data

Order number	130650 G1/8
GTIN	4045197067753
Item class	12G

Description

Version:

2-piece set **comprising taper and plug tap.**

Application:

For Whitworth parallel pipe threads DIN-ISO 228/1 (threads that do not form a seal within the connection).

Tool material: HSS

Threads per inch: 28

Thread Ø: 9.73 mm

Overall length L: 63 mm

Shank Ø D_s: 7 mm

Shank square □: 5.5 mm

Tapping hole Ø: 8.8 mm

Technical description

Thread pitch	0.907 mm
Threads per inch	28
Tapping hole Ø	8.8 mm
Thread Ø	9.73 mm
Tool material	HSS

Shank $\varnothing D_s$	7 mm
Overall length L	63 mm
Shank square \square	5.5 mm
Thread depth	29.19 mm
Thread size	G1/8
Coating	uncoated
Thread type	G
Flank angle	55°
Standard	DIN 5157
Taper lead form	C
Taper lead form	D
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes and through holes
Cutting direction	right-hand
Type of threading tool	Hand tap
Colour ring	without
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions		
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		

Steel < 900 N/mm ²	suitable
GG(G)	suitable only under restricted conditions
Uni	Suitable
Oil	suitable
dry	suitable only under restricted conditions