

**Garant**
**Solid carbide reamer HPC through hole, TiAlN, Nominal  $\varnothing$  DC: 4mm**

**Order data**

Order number	164350 4
GTIN	4045197328403
Item class	10N

**Description**
**IMPORTANT: item is configurable**

 Nominal  $\varnothing$  D<sub>C</sub>: 4 mm

 $\varnothing$  range: 3.7 - 4.2 mm, Intervall: 0,001

**Version:**

**Version suitable for NC** with straight shank  $\varnothing$  for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short flutes and left-hand helix.

**Application:**

 For **HPC/HSM reaming** of **through holes**.

**Note:**
**NEW GENERATION AVAILABLE!**
**Recommended successor product is No. 164420.**

Application for type of drilling: for through holes

Number of cutting edges Z: 4

 $\varnothing$  range: 3.7 - 4.2 mm

 Flute length L<sub>C</sub>: 12 mm

 Overhang L<sub>1</sub>: 34 mm

Overall length L: 75 mm

Number of cutting edges Z: 4

 Shank  $\varnothing$  D<sub>S</sub>: 6 mm

**Technical description**

Shank tolerance	h6
-----------------	----

Feed f in stainless steel < 900 N/mm <sup>2</sup>	0.06 mm/rev.
Overhang L <sub>1</sub>	34 mm
Nominal Ø D <sub>c</sub>	4 mm
Shank Ø D <sub>s</sub>	6 mm
Overall length L	75 mm
Flute length L <sub>c</sub>	12 mm
Ø range	3.7 - 4.2 mm
Number of cutting edges Z	4
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for through holes
Colour ring	blue
Type of product	Phillips bit

## User data

	Suitability	V <sub>c</sub>	ISO code
INOX < 900 N/mm <sup>2</sup>	suitable	30 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	25 m/min	M
Oil	suitable		
wet maximum	suitable		