

Garant
Solid carbide reamer HPC blind hole, DLC, Nominal \varnothing DC: 19 mm

Order data

Order number	164347 19
GTIN	4045197548986
Item class	10N

Description
Version:

Version suitable for NC with straight shank \varnothing for standard arbors especially in **hydraulic chucks** or **high precision collet chucks**. This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

Reamers finish ground to match your specifications.

With the latest generation of **DLC coating sp²**.

Application:

For **HPC/HSC reaming of blind holes**.

Number of cutting edges Z: 6

\varnothing range: 18.21 - 19.2 mm

Flute length L_c: 25 mm

Overhang L₁: 95 mm

Overall length L: 150 mm

Number of cutting edges Z: 6

Shank \varnothing D_s: 20 mm

Technical description

Overhang L ₁	95 mm
Feed f in cast alu	1.7 mm/rev.
Shank tolerance	h6
Nominal \varnothing D _c	19 mm
Shank \varnothing D _s	20 mm
Overall length L	150 mm

Flute length L_c	25 mm
Ø range	18.21 - 19.2 mm
Number of cutting edges Z	6
Coating	DLC
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	yellow
Type of product	Reaming tool with non-detachable cutters