

**Garant****T-tap wrench with ratchet, All-steel, Overall length: 85mm**

## Order data

Order number	148700 85
GTIN	4045197511102
Item class	11K

## Description

### Version:

With two-jaw chuck for clamping square shanks. Moveable T-handle with a groove at each end for engaging the retaining ball. Bracket chrome-plated. Ratchet is reversible and can also be locked. **All-steel construction** for high torque applications. Toolholder with precision concentricity and tight tolerances. Clamping jaws milled and induction hardened for high toughness and optimum surface hardness.

### Application:

Suitable for tapping holes where access is difficult.

### Note:

The square sizes of other tap and reamer sizes can be found in the tables in the respective Product Groups.

## Technical description

Capacity <input type="checkbox"/>	2.6 - 5.5 mm
Overall length	85 mm
for hand taps DIN 352	M3 – M10

Spare jaws No. 148710 size	85
Material	All-steel
Type of product	Pin vice