

Garant**Machine tap, vaporised, MF: 3X0,35****Order data**

Order number	136210 3X0,35
GTIN	4045197078506
Item class	11H

Description**Version:**

Surface vaporised for reduced edge build-up.

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2 6H

Thread pitch: 0.35 mm

Overall length L: 56 mm

Shank $\varnothing D_s$: 2.2 mmTapping hole \varnothing : 2.65 mm**Technical description**

Thread \varnothing	3 mm
Thread pitch	0.35 mm
Number of clamping slots	3
Number of cutting edges Z	3
Tapping hole \varnothing	2.65 mm
Shank $\varnothing D_s$	2.2 mm
Overall length L	56 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Standard	DIN 374

Thread depth	9 mm
Thread type	MF
Thread size	M3×0.35
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Type of product	Tap

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	13 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		
wet maximum	suitable		