Garant

Solid carbide reamer HPC blind hole, DLC, Nominal Ø DC: 8H7 mm



Order data

| Order number | 164347 8H7 |
|--------------|---------------|
| GTIN | 4045197592316 |
| Item class | 10N |

Description

Version:

Version suitable for NC with straight shank Ø for standard arbors especially in **hydraulic chucks** or **high precision collet chucks.** This gives **very high concentricity** and **process reliability**. No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

Reamers finish ground to match your specifications.

With the latest generation of **DLC coating sp**².

Application:

For HPC/HSC reaming of blind holes.

Bore Ø tolerance: H7 Number of cutting edges Z: 6 Bore Ø tolerance: H7 Flute length L_c : 16 mm Overhang L_1 : 60 mm Overall length L: 100 mm Number of cutting edges Z: 6 Shank Ø D_c : 8 mm

Technical description

| Nominal Ø D _c | 8 mm |
|--------------------------|-------------|
| Shank tolerance | h6 |
| Overhang L ₁ | 60 mm |
| Feed f in cast alu | 1.4 mm/rev. |
| Shank Ø D _s | 8 mm |

| Overall length L | 100 mm |
|---------------------------------------|--|
| Flute length L _c | 16 mm |
| Number of cutting edges Z | б |
| recommended drill Ø in cast aluminium | 7.9 mm |
| Bore Ø tolerance | H7 |
| Coating | DLC |
| Tool material | Solid carbide |
| Standard | Manufacturer's standard |
| Туре | W |
| Through-coolant | yes, with 25 bar |
| Shank | DIN 6535 HA with h6 |
| Machining strategy | HPC |
| Application for type of drilling | for blind holes |
| Colour ring | yellow |
| Type of product | Reaming tool with non- detachable cutters |