

**Garant**
**Machine tap, vaporised, M: M3**

**Order data**

Order number	131100 M3
GTIN	4045197068446
Item class	11H

**Description**
**Version:**
**Strong spiral point.**

**Guide section with oil grooves**, but without chip flutes. **Particularly strong, optimal self-guidance with no recutting** on reversal.

Sizes M2.3 and M2.6 to the old DIN profile.

**Callout:**

Oil groove

Guide thread

Lead-in

Spiral point

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 0.5 mm

Overall length L: 56 mm

Shank  $\varnothing$  D<sub>s</sub>: 3.5 mm

Shank square □: 2.7 mm

Tapping hole  $\varnothing$ : 2.5 mm

**Technical description**

Tapping hole $\varnothing$	2.5 mm
Thread $\varnothing$	3 mm
Number of cutting edges Z	2
Number of clamping slots	2

Thread pitch	0.5 mm
Standard	DIN 371
Shank $\varnothing D_s$	3.5 mm
Overall length L	56 mm
Shank square $\square$	2.7 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	9 mm
Thread type	M
Thread size	M3
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	13 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P

CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		
wet maximum	suitable		