

Garant**Machine tap, vaporised, M: M8****Order data**

Order number	131100 M8
GTIN	4045197068491
Item class	11H

Description**Version:****Strong spiral point.**

Guide section with oil grooves, but without chip flutes. **Particularly strong, optimal self-guidance with no recutting** on reversal.

Sizes M2.3 and M2.6 to the old DIN profile.

Callout:

Oil groove

Guide thread

Lead-in

Spiral point

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 2 6H

Thread pitch: 1.25 mm

Overall length L: 90 mm

Shank \varnothing D_s: 8 mm

Shank square □: 6.2 mm

Tapping hole \varnothing : 6.8 mm

Technical description

Tapping hole \varnothing	6.8 mm
Thread pitch	1.25 mm
Number of clamping slots	3
Thread \varnothing	8 mm

Number of cutting edges Z	3
Standard	DIN 371
Shank $\varnothing D_s$	8 mm
Overall length L	90 mm
Shank square \square	6.2 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	24 mm
Thread type	M
Thread size	M8
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	yellow
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	13 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P

CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		
wet maximum	suitable		