

**Garant**
**Machine tap for synchronised spindles HSS-E-PM, DLC, M: M16**

**Order data**

Order number	131125 M16
GTIN	4045197648525
Item class	11H

**Description**
**Version:**

**Sturdy design with spiral point and shank to DIN 1835-B.** Special geometry for use on machines with **synchronised spindle drives**. Guidance is provided by the synchronising spindle of the machine.

With the latest generation of special **DLC coating sp<sup>2</sup>** for optimum tool life.

For use with **emulsion** (fat content minimum 8%).

**Note:**

**For use on synchronised spindles,** the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures very high process reliability.

Thread type: M

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 2 mm

Overall length L: 110 mm

Shank Ø D<sub>s</sub>: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 14 mm

**Technical description**

Thread pitch	2 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread Ø	16 mm

Tapping hole $\varnothing$	14 mm
Standard	Manufacturer's standard
Shank $\varnothing D_s$	12 mm
Overall length L	110 mm
Shank square $\square$	9 mm
Tolerance class	ISO 2X 6HX
Tool material	HSS E PM
Thread depth	40 mm
Thread type	M
Thread size	M16
Coating	DLC
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	DIN 1835 B with h6
Through-coolant	no
Application for type of drilling	up to 2.5xD for through holes
Cutting direction	right-hand
Shank tolerance	h6
Type of threading tool	Machine tap for synchronous machining
Colour ring	yellow
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Aluminium	suitable	30 m/min	N
Aluminium (short chipping)	suitable	30 m/min	N
Alu > 10% Si	suitable	25 m/min	N

PMMA acrylic	suitable	25 m/min	N
AFRP aramid	suitable only under restricted conditions	5 m/min	N
PA 66 GF30	suitable only under restricted conditions	15 m/min	N
PTFE CF25	suitable	25 m/min	N
Cu	suitable	55 m/min	N
CuZn	suitable	35 m/min	N
GRP	suitable only under restricted conditions	6 m/min	N
CRP	suitable only under restricted conditions	4 m/min	N
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		