

Garant
Machine taps, uncoated, MF: 26X1,5

Order data

Order number	136250 26X1,5
GTIN	4045197078995
Item class	11H

Description
Version:
Sturdy design, with 15° right-hand chip flutes.

Thread type: MF

Tool material: HSS E

Standard: DIN 374

Tolerance class: ISO 2 6H

Thread pitch: 1.5 mm

Overall length L: 140 mm

 Shank $\varnothing D_s$: 18 mm

 Shank square \square : 14.5 mm

 Tapping hole \varnothing : 24.5 mm

Technical description

Number of clamping slots	4
Tapping hole \varnothing	24.5 mm
Thread pitch	1.5 mm
Number of cutting edges Z	4
Thread \varnothing	26 mm
Shank $\varnothing D_s$	18 mm
Overall length L	140 mm
Shank square \square	14.5 mm
Tolerance class	ISO 2 6H

Tool material	HSS E
Standard	DIN 374
Thread depth	52 mm
Thread type	MF
Thread size	M26×1.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	15°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

