

**Garant****Machine tap, left-hand thread HSS-E 6H, vaporised, M-LH: M16****Order data**

Order number	136180 M16
GTIN	4045197078469
Item class	11H

**Description****Version:**

**Left-hand cutting.** With **strong left-hand chip flutes**, for optimum swarf evacuation.

Thread type: M-LH

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 110 mm

Shank  $\varnothing D_s$ : 12 mm

Shank square  $\square$ : 9 mm

Tapping hole  $\varnothing$ : 14 mm

**Technical description**

Number of clamping slots	3
Tapping hole $\varnothing$	14 mm
Thread pitch	2 mm
Number of cutting edges Z	3
Thread $\varnothing$	16 mm
Standard	DIN 376
Shank $\varnothing D_s$	12 mm
Overall length L	110 mm
Shank square $\square$	9 mm

Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	48 mm
Thread type	M-LH
Thread size	M16 LH
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	left-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable only under restricted conditions	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	6 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	13 m/min	N

Uni	suitable
Oil	suitable
wet maximum	suitable only under restricted conditions