

**Garant**
**Machine tap 6G DIN 371, uncoated, M: M3,5**

**Order data**

Order number	131300 M3,5
GTIN	4045197069603
Item class	11H

**Description**
**Version:**
**With spiral point.**
**Tolerance class ISO 3 / 6G** = oversize 0.02 – 0.04 mm.

**Application:**

For components which are **galvanised** after threading or shrink slightly when hardened.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 3 6G

Thread pitch: 0.6 mm

Overall length L: 56 mm

Shank  $\varnothing D_s$ : 4 mm

Shank square  $\square$ : 3 mm

Tapping hole  $\varnothing$ : 2.9 mm

**Technical description**

Tapping hole $\varnothing$	2.9 mm
Thread pitch	0.6 mm
Number of cutting edges Z	3
Number of clamping slots	3
Thread $\varnothing$	3.5 mm
Standard	DIN 371
Shank $\varnothing D_s$	4 mm

Overall length L	56 mm
Shank square □	3 mm
Tolerance class	ISO 3 6G
Tool material	HSS E
Thread depth	10.5 mm
Thread type	M
Thread size	M3.5
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

