

**Garant**
**Machine tap HSS-E-PM, vaporised, MF: 26X1,5**

**Order data**

Order number	137055 26X1,5
GTIN	4045197585493
Item class	11H

**Description**
**Version:**

Surface vaporised for reduced edge build-up.

Thread type: MF

Tool material: HSS E PM

Standard: DIN 374

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 140 mm

Shank  $\varnothing D_s$ : 18 mm

Shank square  $\square$ : 14.5 mm

Tapping hole  $\varnothing$ : 24.5 mm

**Technical description**

Tapping hole $\varnothing$	24.5 mm
Thread pitch	1.5 mm
Number of clamping slots	4
Number of cutting edges Z	4
Thread $\varnothing$	26 mm
Shank $\varnothing D_s$	18 mm
Overall length L	140 mm
Shank square $\square$	14.5 mm
Tolerance class	ISO 2X 6HX

Tool material	HSS E PM
Standard	DIN 374
Thread depth	52 mm
Thread type	MF
Thread size	M26×1.5
Coating	vaporised
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	20°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	pink
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable only under restricted conditions	18 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	9 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	3 m/min	P
Ti > 850 N/mm <sup>2</sup>	suitable	4 m/min	S
Oil	suitable		
wet maximum	suitable		