

Garant**Machine tap 6G DIN 371, uncoated, M: M10****Order data**

Order number	131300 M10
GTIN	4045197069658
Item class	11H

Description**Version:****With spiral point.****Tolerance class ISO 3 / 6G** = oversize 0.02 – 0.04 mm.**Application:**For components which are **galvanised** after threading or shrink slightly when hardened.

Thread type: M

Tool material: HSS E

Standard: DIN 371

Tolerance class: ISO 3 6G

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank Ø D_s: 10 mm

Shank square □: 8 mm

Tapping hole Ø: 8.5 mm

Technical description

Number of cutting edges Z	3
Number of clamping slots	3
Thread pitch	1.5 mm
Tapping hole Ø	8.5 mm
Thread Ø	10 mm
Standard	DIN 371
Shank Ø D _s	10 mm

Overall length L	100 mm
Shank square □	8 mm
Tolerance class	ISO 3 6G
Tool material	HSS E
Thread depth	30 mm
Thread type	M
Thread size	M10
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

