

Garant
Spiral point tap short, uncoated, M: M2,5

Order data

Order number	131450 M2,5
GTIN	4045197069733
Item class	11H

Description
Version:
With spiral point.
Application:
As hand or machine tap.

Thread type: M

Tool material: HSS E

Standard: DIN 352

Tolerance class: ISO 2 6H

Thread pitch: 0.45 mm

Overall length L: 40 mm

 Shank $\varnothing D_s$: 2.8 mm

 Shank square \square : 2.1 mm

 Tapping hole \varnothing : 2.05 mm

Technical description

Number of cutting edges Z	2
Thread \varnothing	2.5 mm
Tapping hole \varnothing	2.05 mm
Thread pitch	0.45 mm
Number of clamping slots	2
Standard	DIN 352
Shank $\varnothing D_s$	2.8 mm

Overall length L	40 mm
Shank square □	2.1 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	7.5 mm
Thread type	M
Thread size	M2.5
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

