

**Garant****Solid carbide reamers HPC blind hole, Diamond, Nominal Ø DC: 11,5 mm****Order data**

Order number	164357 11,5
GTIN	4045197513908
Item class	10N

**Description****Version:**

With the latest generation of **crystalline diamond coating sp<sup>3</sup>**, for process reliability in machining **fibre-reinforced composites, CRP, GRP, and graphite**.

**Version** suitable for NC with straight shank Ø for standard arbors especially in **hydraulic chucks or high precision collet chucks**. This gives **very high concentricity and process reliability**.

No need to procure special collets. With internal coolant supply for **HPC applications** to reduce manufacturing costs.

**Reamers finish ground to match your specifications.**

With short, straight flutes.

**Application:**

For **HPC/HSC reaming of blind holes**.

Number of cutting edges Z: 6

Ø range: 11.21 - 11.7 mm

Flute length L<sub>c</sub>: 20 mm

Overhang L<sub>i</sub>: 71 mm

Overall length L: 120 mm

Number of cutting edges Z: 6

Shank Ø D<sub>s</sub>: 12 mm

**Technical description**

Feed f in PEEK CF30	1.5 mm/rev.
Shank tolerance	h6
Nominal Ø D <sub>c</sub>	11.5 mm
Feed f in GRP CRP	1 mm/rev.

Overhang L <sub>1</sub>	71 mm
Shank Ø D <sub>s</sub>	12 mm
Overall length L	120 mm
Flute length L <sub>c</sub>	20 mm
Ø range	11.21 - 11.7 mm
Number of cutting edges Z	6
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Through-coolant	yes, with 25 bar
Shank	DIN 6535 HA with h6
Machining strategy	HPC
Application for type of drilling	for blind holes
Colour ring	black
Type of product	Reaming tool with non-detachable cutters