

**Garant****Machine tap, uncoated, M: M14****Order data**

Order number	131700 M14
GTIN	4045197070104
Item class	11H

**Description****Version:****Sturdy design with 15° left-hand spiral.****Advantage:****Particularly suitable for interrupted cuts** (e.g. longitudinal groove in the hole).

Thread type: M

Tool material: HSS E

Standard: DIN 376

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 110 mm

Shank  $\varnothing D_s$ : 11 mmShank square  $\square$ : 9 mmTapping hole  $\varnothing$ : 12 mm**Technical description**

Thread pitch	2 mm
Number of clamping slots	3
Number of cutting edges Z	3
Thread $\varnothing$	14 mm
Tapping hole $\varnothing$	12 mm
Standard	DIN 376
Shank $\varnothing D_s$	11 mm

Overall length L	110 mm
Shank square □	9 mm
Tolerance class	ISO 2 6H
Tool material	HSS E
Thread depth	42 mm
Thread type	M
Thread size	M14
Coating	uncoated
Flank angle	60 °
Thread standard	DIN 13
Taper lead form	D
Helix angle	15-20 °
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

## User data

	Suitability	V <sub>c</sub>	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	15 m/min	P
GG(G)	suitable only under restricted conditions	9 m/min	K
Oil	suitable		

wet maximum

---

suitable only under  
restricted conditions