

**Garant**
**Machine tap, uncoated, UNC: 7/16-14**

**Order data**

Order number	137860 7/16-14
GTIN	4045197080226
Item class	11H

**Description**
**Version:**
**Sturdy design, with right-hand chip flutes. HSS-E**
**Application:**
**For UNC uniform coarse threads ASME – B1.1.**

Thread type: UNC

Tool material: HSS E

Standard: DIN 376

Threads per inch: 14

Thread Ø: 11.11 mm

Overall length L: 100 mm

 Shank Ø D<sub>s</sub>: 8 mm

Shank square □: 6.2 mm

Tapping hole Ø: 9.4 mm

**Technical description**

Number of clamping slots	3
Thread pitch	1.814 mm
Tapping hole Ø	9.4 mm
Number of cutting edges Z	3
Threads per inch	14
Thread Ø	11.11 mm
Standard	DIN 376

Tool material	HSS E
Shank $\varnothing D_s$	8 mm
Overall length L	100 mm
Shank square $\square$	6.2 mm
Thread depth	22.22 mm
Thread type	UNC
Thread size	7/16-14 UNC
Coating	uncoated
Flank angle	60°
Tolerance class	2B
Taper lead form	C
Helix angle	20°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2xD for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	15 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

