

Garant
Machine tap, uncoated, UNC: 4-40

Order data

Order number	137860 4-40
GTIN	4045197080134
Item class	11H

Description
Version:
Sturdy design, with right-hand chip flutes. HSS-E
Application:
For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E

Standard: DIN 371

Threads per inch: 40

 Thread \varnothing : 2.84 mm

Overall length L: 56 mm

 Shank \varnothing D_s: 3.5 mm

 Shank square \square : 2.7 mm

 Tapping hole \varnothing : 2.35 mm

Technical description

Tapping hole \varnothing	2.35 mm
Threads per inch	40
Number of cutting edges Z	3
Thread \varnothing	2.84 mm
Thread pitch	0.635 mm
Number of clamping slots	3
Standard	DIN 371
Tool material	HSS E

Shank $\varnothing D_s$	3.5 mm
Overall length L	56 mm
Shank square \square	2.7 mm
Thread depth	5.7 mm
Thread type	UNC
Thread size	4-40 UNC
Coating	uncoated
Flank angle	60°
Tolerance class	2B
Taper lead form	C
Helix angle	20°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Oil	suitable		
wet maximum	suitable only under restricted conditions		

