

Garant
Machine tap long, uncoated, M: M16

Order data

Order number	131800 M16
GTIN	4045197070418
Item class	11H

Description
Version:
Long shank (with tapered shank Ø for greater operating depths).
Advantage:

Particularly suitable **for tapping holes where access is difficult.**

Thread type: M

Tool material: HSS

Standard: DIN 357

Tolerance class: ISO 2 6H

Thread pitch: 2 mm

Overall length L: 200 mm

Shank Ø D_s: 12 mm

Shank square □: 9 mm

Tapping hole Ø: 14 mm

Technical description

Tapping hole Ø	14 mm
Number of cutting edges Z	3
Thread pitch	2 mm
Thread Ø	16 mm
Number of clamping slots	3
Standard	DIN 357
Shank Ø D _s	12 mm
Overall length L	200 mm

Shank square <input type="checkbox"/>	9 mm
Tolerance class	ISO 2 6H
Tool material	HSS
Thread depth	32 mm
Thread type	M
Thread size	M16
Coating	uncoated
Flank angle	60°
Thread standard	DIN 13
Taper lead form	A
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for conventional machining
Colour ring	without
Type of product	Tap

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable	15 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
GG(G)	suitable only under restricted conditions	9 m/min	K
Oil	suitable		
wet maximum	suitable only under restricted conditions		

