



Workshop compressor, Type: 210/10W



Order data

Order number	079841 210/10W
GTIN	2050001676542
Item class	03R

Description

Version:

Corrosion-free valves, highly efficient cooling, maintenance-free transmission components, corrosion-protected reservoir, minimum 10-year spare parts availability guarantee. High efficiency for low operating costs. Compact small compressor with sturdy wheels for smaller air requirements.

Supplied with:

Filter pressure regulator with manometer, quick-release connection.

Note:

Other workshop compressors available on request.

Technical description

Pressure vessel volume	10 l
maximum filling rate	140 l/min
Weight	29 kg
Length	420 mm
maximum suction rate	210 l/min

Power consumption	1.1 kW
Height	650 mm
maximum pressure (air)	10 bar
Width	370 mm
Manufacturer's designation	210/10W
Type of product	Compressor