

Garant
Fluteless machine tap without oil grooves HSS-E-PM 6HX, TiN, M: M10

Order data

Order number	139115 M10
GTIN	4045197508584
Item class	11H

Description
Version:
DIN 2174 (\approx **DIN 371** \leq M10; \approx **DIN 376** \geq M12).

The **innovative polygon form** permits a wide application spectrum. The **multi-function layer structure** achieves **maximum service life** even in **high-tensile materials**.

Tolerance class: ISO 2X 6HX

Thread pitch: 1.5 mm

Overall length L: 100 mm

Shank \varnothing D_s: 10 mm

Shank square □: 8 mm

Tapping hole \varnothing guide value: 9.35 mm

Technical description

Number of cutting edges Z	5
Thread \varnothing	10 mm
Thread pitch	1.5 mm
Number of clamping slots	5
Shank \varnothing D _s	10 mm
Shank square □	8 mm
Overall length L	100 mm
Tapping hole \varnothing guide value	9.35 mm
Tolerance class	ISO 2X 6HX
Thread depth	15 mm

Thread size	M10
Coating	TiN
Thread type	M
Flank angle	60 °
Tool material	HSS E PM
Standard	DIN 2174
Thread standard	DIN 13
Taper lead form	C
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 1.5×D for through holes
Application for type of drilling	up to 1.5×D for blind holes
Cutting direction	right-hand
Colour ring	blue
Type of product	Fluteless tap

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	32 m/min	P
Steel < 750 N/mm ²	suitable	27 m/min	P
Steel < 900 N/mm ²	suitable	22 m/min	P
Steel < 1100 N/mm ²	suitable	17 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	7 m/min	M
CuZn	suitable only under restricted conditions	22 m/min	N
Oil	suitable		
wet maximum	suitable		

